


No.	Description	Code	Fixings Included
1	600 Pursuit Drawer Unit	PUR600W/CE/AE	Wallmounted Brackets
2	900 Pursuit Drawer Unit	PUR900W/CE/AE	Wallmounted Brackets
3	1200 Pursuit Column	PURCMIR12W/CE/AE	Wallmounted Brackets Shelf Clips
4	Internal Wooden Boxes - Set of 3	BOXSET3	No



Finishes Available	
	Gloss White
	Charcoal Elm
	Alpine Elm

\*Basin Not Included  
\*Grain on side panels vertical, front panels are horizontal.


## Dimensions - Pursuit 600



Diagrams not to scale  
All dimensins in mm  
tolerance of +5mm


Dimensions - Pursuit 900

Diagrams not to scale  
All dimensins in mm  
tolerance of +5mm




Dimensions - Pursuit 1200

Diagrams not to scale  
All dimensins in mm  
tolerance of +5mm




Dimensions - Pursuit 1200

Diagrams not to scale  
All dimensins in mm  
tolerance of +5mm




### Dimensions - Pursuit 1200 Wall Columnn



Diagrams not to scale  
All dimins in mm  
tolerance of +5mm

### Internal Storage



### Solid Surface

Solid surface. what is it?

- A homogenous compound mixture of polyester and aluminium trihydrate.
- Aluminium trihydrate is derived from a natural Bauxite ore
- Moulded, vacuum treated and then finished by hand to create a perfectly smooth matt finish which is highly dimensionally accurate.


-Fully tested:

- Point impacts (255g ball dropped from 610mm)
- Stain resistant
- Colourfast
- Temperature resistance
- Can be sanded and refinished should any stains occur due to misuse.

Low Profile Trap

Low profile trap required for use with Pursuit  
 Supplied by Wirquin  
 Can be used flat or bent down to join plumbing  
 Operates using syphoning action to create air trap

Testing  
 1000000 Cycle testing  
 Thermal shocking 15mn at 95°C then 10mn at 20°C  
 Passing of standard water testing elements



FAQ's

- Q. Are any components shared?  
 A. -Hangers for column and runners on units are new  
 -Column glass shelf supports same as Vista  
 -WM unit hangers are the same as Vista, Cypher, Moment
  
- Q. Are the worktops pre-drilled?  
 A. No. These can be cut using standard woodmaking tools
  
- Q. Are the handles pre-drilled?  
 A. Yes and they are pre-fitted.
  
- Q. I cannot do vertical adjustment on column hangers  
 A. Remove the column from the wall loosen hangers from the back. Mount back on brackets and adjust.
  
- Q. How do you reverse the door on the column?  
 A. Turn the column upside-down. There are hangers on the top and bottom.